

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-FD05.0W

		REVISIONS	DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398						
DCP#	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
1827	Α	RELEASED	но	3/29/08	JN	2/18/08	JN	2/18/08	



The Catch-All cup is a 16-oz. static dissipative general purpose cup designed for the purpose of holding pens, rulers, swabs and other miscellaneous items. Safe for all work areas. This ESD safe cup offers an average surface resistivity of  $10^9$  to  $10^{10}\Omega$  that will dissipate a  $\pm 5000V$  charge in less than 2 seconds at 40% relative humidity.

Note, Contents shown in the cup are not included

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HERBIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL. THE
USER SHALL DETERMINE THE SUTABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSDEVER IN CONNECTION THEREMITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY: HISHAM ODISH	DATE: 3/29/05	DRAWING TITLE:  16 DZ CATCH-ALL CUP, ESD SAFE								
CHECKED BY:	CHECKED BY: DATE:		DWG. NO.			ELEC	TRONIC FIL	.E		REV
Jason Nash	Jason Nash 2/18/08		A 1469		10N692.DWG				Α	
APPROVED BY:	PROVED BY: DATE:				5 3					
Jasn Nash	2/18/08	SCALE: NTS			и.о.м.: INCHES [mm]		SHEET: 1		OF	1