# System 250 Data Sheet

The new BOFA system 250 is a compact high volume unit designed to extract fumes through a variety of extraction accessories. The system comes complete with a user friendly installation kit allowing instant extraction for minimum fuss and cost.

### Carcass

Main body, central support, lid and base are powder coated Zintac

#### Standard Equipment

Weight: 10kg

Filter Indication light Noise level: below 55dba

Integral silencer with air exhausted out

the base of unit

Standard Filter set (see below)

2 x 50mm Diameter inlet

Thermal trip

System 250 Installation Kit (table brackets, Flip-Top connectors, mounting plates,

adaptors with balancing valves & flexi tubing)

#### **Electrics**

230v 1ph 50hz or 110v 1ph 60hz 2m Power Cord **Fused IEC illuminated switch** 

Full load current: 1.5 amps


#### Warranty

12 month warranty

12 month COSHH Certification

(when installed by BOFA engineers)

## 50.00mm 50.00mm 75.00mm 15.00mm 420.00mm 370.00mm 15.00mm





The system 250 comes complete with the installation kit shown opposite x 2. This includes 3 meters of 50mm flexible tubing, 2 x table brackets & mounting plates,

2 x flush system seal Flip top connector and adaptor with balancing valve.

#### Standard Filter Set

#### Pre Filter

95% efficiency @ 0.8micron

#### **Combined Filter**

HEPA 99.997% @ 0.3 micron

Gas Filter media

**Activated carbon impregnated** with potassium permanganate

### **HEPA Filter** Efficiency 99.997% @ 0.3 micror Efficiency 95% @ 0.8 micron Gas Filter media Activated Carbon impregnated with potassium permanganate

#### Maximum number of arms


32mm <u>50mm</u> <u>75mm</u> EC: 4 EC: 2 EC: 1 **US: 4** US: 2 EC: 1

Blower / Pump

**Radial Ventilator** 40,000 life hours Pressure 40m/bar 0.12k Output Airflow 180m3/hr (with filters fitted) IP54 Synchronous (brushless) motor

#### Options


**VOC Monitoring** 



The chart opposite shows the maximum number of soldering arms that the System 250 is capable of extracting from.

> The chart opposite showe the performance of the pump within the System 250. The performance curve also highlights the effect of new filters on the new System 250's vacuum capabilities

gBC gL



100 r



