
Fair-Rite Products Corp. Your Signal Solution®

Fair-Rite Products Corp. PO Box J,One Commercial Row, Wallkill, NY 12589-0288 Phone: (888) 324-7748 www.fair-rite.com



Fair-Rite Product's Catalog Part Data Sheet, 2843000202 Printed: 2010-11-09



Figure 1

Part Number: 2843000202

Frequency Range: Suppression Applications for Broadband Frequencies 20-300 MHz (43 material)

Description: 43 MULTI-APERTURE CORE

Application: Suppression Components

Where Used: Board Component

Part Type: Multi-Aperture cores

Preferred Part:

Mechanical Specifications

Weight: 3.700 (g)

Part Type Information

Multi-aperture cores are used in suppression applications and in balun (balance-unbalance) and other broadband transformers. They are also employed in airbag designs to prevent accidental activation.

-All multi-aperture cores are supplied burnished.

-Multi-aperture cores in 73 and 43 materials are controlled for impedance only. The 61 NiZn material is controlled for both impedance and AL value. The high frequency 67 material is controlled for AL value. All listed impedance values are typical values. Minimum impedance values are specified for the + marked frequencies. The minimum guaranteed impedance is the listed typical impedance less 20%.

-Multi-aperture cores in 73 and 43 material are measured for impedance on the 4193A Vector Impedance Analyzer. The 61 multi-aperture cores are tested on the 4191A Impedance Analyzer. All impedance measurements are performed with a single turn to both holes, using the shortest practical wire length.

-The 61 and 67 material multi-hole beads are tested for AL value. The test frequency is 10 kHz at < 10 gauss. The test winding is five turns wound through both holes.

-Preferred multi-aperture cores are the suggested choice for new designs. Samples are readily available and orders have typically shorter lead times than other multi-aperture cores. For any multi-aperture requirement not listed here, feel free to contact our customer service group for availability and pricing.

-Our 'Multi-Aperture Core Kit' (part number 0199000036) is available for proto type evaluation.

-Explanation of Part Numbers: Digits 1&2 = product class, 3&4 = material grade last digit 2 = burnished.

Fair-Rite Products Corp. Your Signal Solution®

Ferrite Components for the Electronics Industry Fair-Rite Products Corp. PO Box J.One Commercial Row, Wallkill, NY 12589-0288 Phone: (888) 324-7748 www.fair-rite.com Fair-Rite Product's Catalog Part Data Sheet, 2843000202 Printed: 2010-11-09



Mechanical Specifications

Dim	mm	mm	nominal	inch
		tol	inch	misc.
А	13.30	±0.60	0.525	-
В	14.35	±0.50	0.565	-
С	7.50	±0.35	0.295	-
D	-	-	-	-
E	5.70	±0.25	0.225	-
F	-	-	-	-
G	-	-	-	-
Н	3.80	±0.25	0.150	-
J	-	-	-	-
К	-	-	-	-

Electrical Specifications

Typical Impedance (Ω)			
25 MHz 123			
100 MHz+ 180			

Electrical Properties	

Land Patterns

\vee	W	Х	Y	Z
	ref			
-	-	-	-	-
-	-	-	-	-

Winding Information

Turns	Wire	1st Wire	2nd Wire
Tested	Size	Length	Length
-	-	-	-

Reel Information

Tape Width	Pitch	Parts 7 "	Parts 13 "	Parts 14 "
mm	mm	Reel	Reel	Reel
-	-	-	-	-

Package Size

Pkg Size
- (-)

Connector Plate

# Holes	# Rows	
-	-	

Legend

+ Test frequency

Preferred parts, the suggested choice for new designs, have shorter lead times and are more readily available.

The column H(Oe) gives for each bead the calculated dc bias field in oersted for 1 turn and 1 ampere direct current. The actual dc H field in the application is this value of H times the actual NI (ampere-turn) product. For the effect of the dc bias on the impedance of the bead material, see figures 18-23 in the application note How to choose Ferrite Components for EMI Suppression.

A ½ turn is defined as a single pass through a hole.

∑I/A - Core Constant

A_e: Effective Cross-Sectional Area

 A_{I} - Inductance Factor $\left(\frac{L}{N^{2}}\right)$

N/AWG - Number of Turns/Wire Size for Test Coil Downloaded from <u>Elcodis.com</u> electronic components distributor I e: Effective Path Length

Ve: Effective Core Volume

NI - Value of dc Ampere-turns



Fair-Rite Product's Catalog Part Data Sheet, 2843000202 Printed: 2010-11-09



Ferrite Material Constants

Specific Heat	0.25 cal/g/⁰C
Thermal Conductivity	10x10 ⁻³ cal/sec/cm/°C
Coefficient of Linear Expansion	8 - 10x10 ⁻⁶ /ºC
Tensile Strength	4.9 kgf/mm ²
Compressive Strength	42 kgf/mm ²
Young's Modulus	15x10 ³ kgf/mm ²
Hardness (Knoop)	650
Specific Gravity	\approx 4.7 g/cm ³
The above quoted properties are typical for Fair-Rite	e MnZn and NiZn ferrites.

See next page for further material specifications.

Fair-Rite Products Corp. Your Signal Solution®

Fair-Rite Products Corp. PO Box J,One Commercial Row, Wallkill, NY 12589-0288 Phone: (888) 324-7748 www.fair-rite.com

This NiZn is our most popular ferrite for suppression of conducted EMI from 20 MHz to 250 MHz. This material is also used for inductive applications such as high frequency common-mode chokes.

EMI suppression beads, beads on leads, SM beads, multi-aperture cores, round cable EMI suppression cores, round cable snap-its, flat cable EMI suppression cores, flat cable snap-its, miscellaneous suppression cores, bobbins, and toroids are all available in 43 material.


Fair-Rite Product's Catalog Part Data Sheet, 2843000202 Printed: 2010-11-09



43 Material Characteristics:


Property	Unit	Symbol	Value
Initial Permeability		μ	800
Flux Density	gauss	В	2900
@ Field Strength	oersted	н	10
Residual Flux Density	gauss	B,	1300
Coercive Force	oersted	He	0.45
Loss Factor	10-6	tan δ/μ _i	250
@ Frequency	MHz		1.0
Temperature Coefficient of Initial Permeability (20 -70°C)	%/°C		1.25
Curie Temperature	°C	Tc	>130
Resistivity	Ωcm	ρ	1x10 ⁵

Percent of Original Impedance vs. Temperature




Measured on a 2643000301 using the HP4291A.

Hysteresis Loop




Measured on a 17/10/6mm toroid at 10kHz.

Complex Permeability vs. Frequency



Measured on a 17/10/6mm toroid using the HP 4284A and the HP 4291A.






Measured on a 17/10/6mm toroid at 100kHz.



Fair-Rite Product's Catalog Part Data Sheet, 2843000202 Printed: 2010-11-09





Impedance, reactance, and resistance vs. frequency.