PRODUCT DATA SHEET



PhlatLight[®] LED Illumination Products


CBT-40 Series

Features

- Extremely high optical output: Over 310 Red Lumens
 Over 725 Green lumens
 Over 150 Blue Lumens
- \bullet High thermal conductivity package junction to heat sink thermal resistance of only 1.8 $^{\circ}\text{C/W}$
- Photonic lattice technology for very high surface brightness and uniform emission
- Large, monolithic chip with surface emitting area of 4 mm²
- High luminous efficacy
- Lumen maintenance of greater than 70% after 60,000 hours
- Environmentally friendly: RoHS compliant
- Variable drive currents: less than 1 A through 10 A
- Currently available in Red, Green and Blue; other colors to follow

Applications

- Entertainment
- · Architectural Lighting
- · Medical Lighting
- · Spot Lighting
- Fiber Coupled Illumination
- · Emergency Vehicle Lighting
- · Machine Vision
- · Projection Systems
- Displays and Signage
- General Illumination



PhlatLight® LEDs, based on Photonic Lattice Technology, enable a new class of illumination applications.

Table of Contents

Technology Overview	2
Test Specifications	2
PhlatLight Bin Codes	3
Product Shipping and Labeling Information	4
Optical and Electrical Characteristics	5
Flux and Spectral Characteristics vs. Temperature	9
Lifetime and Lumen Maintenance	9
Spectral Characteristics	9
Radiation Patterns	10
Thermal Resistance	10
Mechanical Dimensions	11
Ordering Information	12



CBT-40 Product Datasheet



Technology Overview

PhlatLight LEDs benefit from a suite of innovations in the fields of chip technology, packaging, and thermal management. These breakthroughs allow illumination designers to achieve efficient light engine designs and deliver high brightness solutions.

PhlatLight Technology

The name PhlatLight is derived from Photonic Lattice. PhlatLight devices use photonic lattice patterns to extract more light from the LED chip, and to create radiation patterns that are collimated compared to typical Lambertian emitters. Optical collection efficiencies improve and optical designs become simplified with a more collimated light source.

Photonic lattice technology creates true surface emission from the source, which enables large area LED chips with uniform brightness over the entire LED chip surface. The optical power and brightness produced by these large monolithic chips enable solutions which replace arc and halogen lamps where arrays of traditional high power LEDs cannot.

Packaging Technology

Thermal management is critical in high power LED applications. With a thermal resistance from junction to heat sink of 1.8 °C/W, PhlatLight CBT-40 devices have the lowest thermal resistance of any LED on the market. This allows the LED to be driven at higher current densities while maintaining a low junction temperature, thereby resulting in brighter and longer lifetimes. The package is easy to use, and ready to be mounted in the lighting system.

Reliability

Designed from the ground up, PhlatLight LEDs are one of the most reliable light sources in the world today. PhlatLight LEDs have passed a rigorous suite of environmental and mechanical stress tests, including mechanical shock, vibration, temperature cycling and humidity, and have been fully qualified for use in extreme high power and high current applications. With very low failure rates and median lifetimes that are well above 60,000 hours, PhlatLight LEDs are ready for the most demanding applications.

Environmental Benefits

PhlatLight LEDs help reduce power consumption and the amount of hazardous waste entering the environment. All PhlatLight products manufactured by Luminus are RoHS compliant and free of hazardous materials, including lead and mercury.

Understanding PhlatLight Test Specifications

Every PhlatLight LED device is fully tested to ensure that it meets the high quality standards of Luminus' products.

Testing Temperature

PhlatLight LEDs are measured in such a way that the characteristics reported agree with how the devices will actually perform when incorporated into a system. This measurement is accomplished by mounting the devices on a 40° C heat sink and allowing the device to reach thermal equilibrium while fully powered. Only after the device reaches equilibrium are the measurements taken. This method of measurement ensures that PhlatLight LEDs perform in the field just as they are specified.

Multiple Operating Points (1.4 A, 5.9 A, 9.8 A)

The tables on the following pages provide typical optical and electrical characteristics. Since the LEDs can be operated over a wide range of drive conditions (currents from <1 A to 10 A, and duty cycle from <1% to 100%) multiple drive conditions are listed.

PhlatLight CBT-40 devices are specified at 5.9 A. The values shown at 1.4 A and 9.8 A are for additional reference at other possible drive conditions.






PhlatLight CBT-40 Bins


PhlatLight LEDs are specified for luminous flux and wavelength at a drive current of 5.9 A (1.5 A/mm²) and placed into one of the following luminous flux (FF) and wavelength (WW) bins:

Blue Bins DH 250 DG 200 Luminous Flux (lumens) 160 DE 120 DD 90 DC 70 DB 50 В5 В7 В9 В6 **B8** Wavelength (nm)



Red Bins ВН 425 BG350 Luminous Flux (lumens) BF 275 BE 215 BD 165 ВС 120 BB 90 R4 R6 R7 R2 R3 R5 R8 Wavelength (nm)





40



WW

PhlatLight Product Shipping and Labeling Information

All PhlatLight products are packaged and labeled with their respective bin as outlined in the tables on page 3. Modules are packaged in trays of 10, with each package only containing one bin. The part number designation is as follows:

C21

Product Family	Chip Area	Color	Package Configuration	Flux Bin	Wavelength Bin
CBT: Chip on Board	40: 4 mm ²	R: Red	C21: 16 x 26.5 mm board	See page 3 for bins	See page 3 for bins
		G: Green			
		B: Blue			

Example: The part number CBT-40-R-C21-BF-R4 refers to a red, CBT-40 module, with a flux range of 275 - 350 lumens and a wavelength range of 619 nm to 623 nm.

Note: Some flux and wavelength bins may have limited availability. Application specific bin kits, consisting of multiple bins, may be available. For ordering information, please refer to page 12 and reference the PhlatLight Binning and Labeling document.





CBT



Reference Optical and Electrical Characteristics (T_{heat sink} = 40 °C)¹

		Red			
Drive Condition ²		1.4 A Continuous	5.9 A Continuous	9.8A Pulsed 50% D.F. ³	
Parameter	Symbol		Values ⁴		Unit
Current Density	j	0.35	1.5	2.5	A/mm ²
	V _{F min}		1.9		٧
Forward Voltage	V _F	2.2	2.5	2.8	٧
	V _{F max}		3.0		٧
Luminous Flux ⁵	Φ _{V typ}	70	270	420	lm
Radiometric Flux	Φ_{r}	0.4	1.6	2.3	W
Luminous Efficacy	η	26	20	18	lm/W
Dominant Wavelength ⁶	λ_{d}	622	623	623	nm
Peak Wavelength	$\lambda_{\mathbf{p}}$	625	628	629	nm
Color Saturation	-	1.00	1.00	1.00	-
FWHM	$\Delta\lambda_{1/2}$	16	19	20	nm
7.8	х	0.695	0.699	0.702	-
Chromaticity Coordinates ^{7,8}	у	0.305	0.301	0.298	-






Yellow squares indicate reference drive conditions






Reference Optical and Electrical Characteristics $(T_{heat \ sink} = 40 \ ^{\circ}C)^{1}$

		Green			
Drive Condition ²		1.4 A Continuous	5.9 A Continuous	9.8 A Pulsed 50% D.F. ³	
Parameter	Symbol		Values ⁴		Unit
Current Density	j	0.35	1.5	2.5	A/mm ²
	V _{Fmin}		3.8		V
Forward Voltage	V _F	3.6	4.5	5.0	٧
	V _{Fmax}		5.3		V
Luminous Flux ⁵	Φγ	240	650	930	lm
Radiometric Flux	Φ_{r}	0.5	1.2	1.9	W
Luminous Efficacy	η	55	28	21	lm/W
Dominant Wavelength ⁶	λ_{d}	535	528	525	nm
Peak Wavelength	λ_{p}	530	524	521	nm
Color Saturation	-	0.91	0.83	0.79	-
FWHM	$\Delta\lambda_{1/2}$	35	39	40	nm
7.8	Х	0.205	0.175	0.161	-
Chromaticity Coordinates ^{7,8}	у	0.740	0.730	0.722	-






Yellow squares indicate reference drive conditions






Reference Optical and Electrical Characteristics $(T_{heat \ sink} = 40 \ ^{\circ}C)^{1}$

		Blue			
Drive Condition ²		1.4 A Continuous	5.9 A Continuous	9.8 A Pulsed 50% D.F. ³	
Parameter	Symbol		Values ⁴		Unit
Current Density	j	0.35	1.5	2.5	A/mm ²
	V _{Fmin}		3.6		٧
Forward Voltage	V _F	3.4	4.2	4.7	٧
	V _{Fmax}		5.3		٧
Luminous Flux ⁵	Φγ	40	110	160	lm
Radiometric Flux	Φ_{r}	0.9	2.2	3.7	W
Luminous Efficacy	η	11	6	5	lm/W
Dominant Wavelength ⁶	λ_{d}	464	464	462	nm
Peak Wavelength	λ_{p}	459	460	460	nm
Color Saturation	-	0.99	0.99	0.99	-
FWHM	$\Delta\lambda_{1/2}$	22	25	27	nm
7.8	x	0.142	0.142	0.142	-
Chromaticity Coordinates ^{7,8}	у	0.036	0.038	0.038	-





Yellow squares indicate reference drive conditions





Reference Optical and Electrical Characteristics (T_{heat sink} = 40 °C)¹

Common Characteristics

	Symbol	Red	Green	Blue	Unit
Emitting Area		4	4	4	mm ²
Emitting Area Dimensions		2.09x1.87	2.09x1.87	2.09x1.87	mm×mm
Dynamic Resistance	Ω_{dyn}	0.08	0.12	0.10	Ω
Thermal Coefficient of Photometric Flux		-0.96	-0.18	-0.007	%/°C
Thermal Coefficient of Radiometric Flux		-0.52	-0.20	-0.17	%/°C
Thermal Coefficient of Junction Voltage		-1.3	-4.6	-3.5	mV/°C

Absolute Maximum Ratings


	Symbol	Red	Green	Blue	Unit
Maximum Current ⁹		12	12	12	Α
Maximum Junction Temperature ¹⁰	T _{jmax}	125	150	150	°C
Storage Temperature Range		-40/+100	-40/+100	-40/+100	°C


- Note 1: All ratings are based on operation with a constant heat sink temperature T_{hs} =40°C. See Thermal Resistance section for T_{hs} definition.
- Note 2: Listed drive conditions are typical for common applications. PhlatLight devices can be driven at currents ranging from <1 A to 12 A and at duty cycles ranging from 1% to 100%. Drive current and duty cycle should be adjusted as necessary to maintain the junction temperature desired to meet application lifetime requirements
- Note 3: Current Density of 2.5 A/mm². Rated at 50% duty cycle and Pulsed operation frequency of f>360Hz; $DC = \frac{t}{T}$
- Note 4: Unless otherwise noted, values listed are typical. Devices are production tested and specified at 5.9 A. Values at 1.4 A and 9.8 A are for reference only.
- Note 5: Total flux from emitting area at listed dominant wavelength. Reported performance is included to show trends for a selected power level. For specific minimum and maximum values, use bin tables. For product roadmap and future performance of devices, contact Luminus.
- Note 6: Minimum and Maximum Dominant Wavelengths are based on typical values +/- 5nm for Red, +/- 8nm for Green and +/- 6nm for Blue.
- Note 7: In CIE 1931 chromaticity diagram coordinates, normalized to X+Y+Z=1.
- Note 8: For reference only.
- Note 9: Luminus PhlatLight LEDs are designed for operation to an absolute maximum current as specified above. Product lifetime data is specified at recommended forward drive currents. Sustained operation at or beyond absolute maximum currents will result in a reduction of device life ime compared to recommended forward drive currents. Actual device lifetimes will also depend on junction temperature. Refer to the lifetime derating curves for further information. In pulsed operation, rise time from 10-90% of forward current should be larger than 0.5 microseconds.
- Note 10: Lifetime dependent on LED junction temperature. Input power and thermal system must be properly managed to ensure lifetime. See charts on pg 7 for further information.
- Note 11: Special design considerations must be observed for operation under 1 A. Please contact Luminus for further information.
- Note 12: Caution must be taken not to stare at the light emitted from these LEDs. Under special circumstances, the high intensity could damage the eye.






Light Output and Spectral Characteristics Over Heat Sink Temperature







Median Lifetime Estimate vs. Tj¹³



Lumen Maintenance¹⁴



Typical Spectrum¹⁵



Note 15. Typical spectrum at current density of 1.5 A/mm² in continuous operation.




Note 13. Median lifetime estimate as a function of junction temperature at 1.5A/mm² in continuous operation. Lifetime defined as time to 70% of initial intensity. Based on preliminary lifetime test data. Data can be used to model failure rate over typical product lifetime.

Note 14. Lumen maintenance vs. time at 1.5A/mm² in continuous operation, Red junction temperature of 70°C, Green junction temperatures of 120°C, Blue junction temperatures of 100°C.




Typical Radiation Pattern


Typical Polar Radiation Pattern for Blue and Green



Typical Polar Radiation Pattern for Red



Thermal Resistance



Typical Thermal Resistance

$R_{\theta j-b}^{1}$	1.63 °C/W
$R_{\theta b-hs}^{1}$	0.19 °C/W
$R_{\theta j-hs}^{2}$	1.82 °C/W
$R_{\theta j\text{-ref}}^{1}$	1.62 °C/W

Note 1: Thermal resistance values are based on FEA model results correlated

to $R_{\theta j-hs}$ data


Note 2: Thermal Resistance is based on eGraf 1205 Thermal interface.

Thermistor Information

The thermistor used in PhlatLight devices mounted on coreboards is from Murata Manufacturing Co. The global part number is NCP15XH103J03RC. Please see http://www.murata.com/ for details on calculating thermistor temperature.

For more information on use of the thermistor, please contact Luminus directly.


Electrical Pinout







Mechanical Dimensions



DIMENSION NAME	DESCRIPTION	NOMINAL DIMENSION	TOLERANCE
"A"	TOP OF METAL SUBSTRATE TO TOP OF GLASS	0.94	±0.13
"B"	EMITTING AREA TO TOP OF GLASS	0.67	± 0.16
"C"	TOP OF METAL SUBSTRATE TO EMITTING AREA	0.27	± 0.05

For detailed drawing of package, please refer to Luminus drawing #DWG-001263

DWG-001263

Connector: MOLEX Part Number 874380843. Please refer to page 10 or detailed drawing for pin-out information.





Ordering Information

Ordering Part Number 1,2,3	Color	Description
CBT-40-R-C21-HC100	Red	Red PhlatLight CBT-40 consisting of a 4 $\rm mm^2$ LED, thermistor, and connector, mounted on a copper-core PCB.
CBT-40-G-C21-JC200	Green	Green PhlatLight CBT-40 consisting of a 4 mm ² LED, thermistor, and connector, mounted on a copper-core PCB.
CBT-40-B-C21-KC300	Blue	Blue PhlatLight CBT-40 consisting of a 4 mm ² LED, thermistor, and connector, mounted on a copper-core PCB.

Note 1: HC100 - denotes a bin kit comprising of all red flux and wavelength bins as specified on page 3

JC200 - denotes a bin kit comprising of all green flux and wavelength bins as specified on page 3

KC300 - denotes a bin kit comprising of all blue flux and wavelength bins as specified on page 3.

See PhlatLight Binning and Labeling document for more information.

Note 2: For info on ordering bin kits, contact your local Luminus sales representative.

Note 3: Standard packaging increment (SPI) is 10.

www.luminus.com

The products, their specifications and other information appearing in this document are subject to change by Luminus Devices without notice. Luminus Devices assumes no liability for errors that may appear in this document, and no liability otherwise arising from the application or use of the product or information contained herein. None of the information provided herein should be considered to be a representation of the fitness or suitability of the product for any particular application or as any other form of warranty. Luminus Devices' product warranties are limited to only such warranties as accompany a purchase contract or purchase order for such products. Nothing herein is to be construed as constituting an additional warranty. No information contained in this publication may be considered as a waiver by Luminus Devices of any intellectual property rights that Luminus Devices may have in such information. PhlatLight[®] is a registered trademark of Luminus Devices, Inc., all rights reserved.

This product is protected by U.S. Patents 6,831,302; 7,074,631; 7,083,993; 7,084,434; 7,098,589; 7,105,861; 7,138,666; 7,166,870; 7,166,871; 7,170,100; 7,196,354; 7,211,831; 7,262,550; 7,274,043; 7,301,271; 7,341,880; 7,344,903; 7,345,416; 7,348,603; 7,388,233; 7,391,059; Patents Pending in the U.S. and other countries.

