


Quick Reference Guide: Stacking Connectors


THINGS TO CONSIDER WHEN SELECTING A MEZZANINE CONNECTOR

- 1. Determine a range of stack heights that will meet the application requirements.
- 2. Determine the minimum number of signals that must pass between the two printed circuit boards (PCBs) with consideration for power and ground.
- 3. Determine how much space is available for the connectors with consideration for its location. Will a traditional two-row connector fit or will a "grid" (many rows) style product work best in the application? The largest pitch that will fit is typically chosen, as larger pitch connectors tend to be more rugged and easier to process.
- 4. Determine the preferred method of attachment. Ball-Grid Array (BGA) products are a variant of surface mount that give connector manufacturers greater co-planarity tolerance than typical surface mount leads. Other types of attachments are solder thru-hole and press-fit thru-hole.
- 5. Determine the connector type, open pin field or controlled impedance, that will best fit the application. Open pin field connectors typically do not have any pre-determined grounds and are usually used in lower speed applications. Tyco Electronics does offer several open pin field connectors that have very good electrical performance characteristics.

HOW TO MEASURE FOR A MEZZANINE CONNECTOR



MOUNTING STYLES



http://www.tycoelectronics.com



Tyco Electronics

PRODUCT SIZES

	d Stack eight inch	Connector Description	Pitch	PCB Attach Method	Туре	Up to 30 Positions	Less than 100 Positions	100 to 200	200 Position and Greater
1.00	0.039	.4mm Fine Stack	.4mm	Smt	Open Pin	Positions	100 Positions	Positions	and Greater
1.50	0.059	.4mm Fine Stack	.4mm	Smt	Open Pin				
1.50	0.059	.5mm Fine Stack	.5mm	Smt	Open Pin				
3.00	0.118	.8mm Fine Stack	.8mm	Smt	Open Pin				
3.90	0.154	.8mm Fine Stack	.8mm	Smt	Open Pin				
4.00	0.157	.5mm Fine Mate	.5mm	Smt	Open Pin				
4.00	0.157	.6mm Free Height	.6mm	Smt	Open Pin				
4.00	0.157	.8mm Fine Mate	.8mm	Smt	Open Pin				
4.20	0.165	.8mm Fine Stack	.8mm	Smt	Open Pin				
4.50	0.177	.5mm Fine Mate	.5mm	Smt	Open Pin				
4.50	0.177	.8mm Fine Mate	.8mm	Smt	Open Pin				
4.70	0.185	.8mm Fine Stack	.8mm	Smt	Open Pin				
5.00	0.197	.5mm Free Height .6mm Free Height	.5mm	Smt	Open Pin				
5.00 5.00	0.197 0.197	.8mm Fine Stack	.6mm .8mm	Smt Smt	Open Pin Open Pin				
5.00	0.197	.8mm Free Height	.8mm	Smt	Open Pin				
5.00	0.197	1.25mm Fine Pitch	1.25mm	Smt	Open Pin				
5.00	0.197	MICTOR SB	.8mm	Smt	Controlled Z				
5.50	0.217	.5mm Fine Mate	.5mm	Smt	Open Pin				
5.90	0.232	.8mm Fine Stack	.8mm	Smt	Open Pin				
6.00	0.236	.5mm Fine Mate	.5mm	Smt	Open Pin				
6.00	0.236	.5mm Free Height	.5mm	Smt	Open Pin				
6.00	0.236	.6mm Free Height	.6mm	Smt	Open Pin				
6.00	0.236	.8mm Free Height	.8mm	Smt	Open Pin				
6.35	0.250	AMPMODU 50/50	.050"	Smt	Open Pin				
6.50	0.256	1.25mm Fine Pitch	1.25mm	Smt	Open Pin				
6.60	0.260	MICTOR	.025"	Smt	Controlled Z	-			
7.00	0.276	.5mm Free Height	.5mm	Smt	Open Pin				
7.00	0.276	.6mm Free Height	.6mm	Smt	Open Pin				
7.00 7.00	0.276 0.276	.8mm Fine Stack .8mm Free Height	.8mm	Smt Smt	Open Pin Open Pin				
7.00	0.276	1.25mm Free Height	1.25mm	Smt	Open Pin				
8.00	0.276	.5mm Free Height	.5mm	Smt	Open Pin				
8.00	0.315	.6mm Free Height	.6mm	Smt	Open Pin				
8.00	0.315	.8mm Free Height	.8mm	Smt	Open Pin				
8.00	0.315	1mm Free Height	1mm	Smt	Open Pin				
8.00	0.315	MICTOR SB	.8mm	Smt	Controlled Z				
8.00	0.315	1.25mm Fine Pitch	1.25mm	Smt	Open Pin				
8.13	0.320	AMPMODU 50/50	.050"	Smt	Open Pin				
9.00	0.354	.5mm Free Height	.5mm	Smt	Open Pin				
9.00	0.354	.8mm Fine Stack	.8mm	Smt	Open Pin				
9.00	0.354	.8mm Free Height	.8mm	Smt	Open Pin				
9.00	0.354	1mm Free Height	1mm	Smt	Open Pin				
9.00	0.354	MICTOR	.025"	Smt	Controlled Z				
9.91	0.390	AMPMODU 50/50	.050"	Smt	Open Pin				
10.00		.6mm Free Height	.6mm	Smt	Open Pin				
	0.394	.8mm Free Height	.8mm	Smt	Open Pin				
	0.394	1 25mm Fine Pitch	1 25mm	Smt	Open Pin				
10.50	0.394	1.25mm Fine Pitch 1.25mm Fine Pitch	1.25mm 1.25mm	Smt Smt	Open Pin Open Pin				
10.50	0.430	Micro-Strip	.050"	Thru-Hole	Controlled Z				
10.92	0.430	MICTOR	.030	Smt	Controlled Z				
11.00	0.433	.5mm Free Height	.5mm	Smt	Open Pin				
11.00	0.433	.6mm Free Height	.6mm	Smt	Open Pin				
11.00	0.433	.8mm Free Height	.8mm	Smt	Open Pin				
11.00	0.433	1mm Free Height	1mm	Smt	Open Pin				
11.00	0.433	1.25mm Fine Pitch	1.25mm	Smt	Open Pin				
11.00	0.433	MICTOR SB	.8mm	Smt	Controlled Z				
2.00	0.472	.5mm Free Height	.5mm	Smt	Open Pin				
12.00	0.472	.6mm Free Height	.6mm	Smt	Open Pin				
12.00	0.472	.8mm Free Height	.8mm	Smt	Open Pin				
12.00	0.472	1mm Free Height	1mm	Smt	Open Pin				
12.57	0.495	MICTOR	.025"	Smt	Controlled Z				
	0.512	.6mm Free Height	.6mm	Smt	Open Pin	_			
	0.512	.8mm Free Height	.8mm	Smt	Open Pin	+			
13.00 13.08		1mm Free Height	1mm	Smt	Open Pin				
	0.515	AMPMODU System 50		Smt	Open Pin				

http://www.tycoelectronics.com



PRODUCT SIZES

		SIZES							
	d Stack eight inch	Connector Description	Pitch	PCB Attach Method	Туре	Up to 30 Positions	Less than	100 to 200	200 Positions
		•	0		O Bi				
14.00	0.551	.8mm Free Height	.8mm	Smt	Open Pin				
14.00	0.551	1mm Free Height	1mm	Smt	Open Pin				
14.00	0.551	MICTOR SB	.8mm	Smt	Controlled Z				
15.00	0.591	.5mm Free Height	.5mm	Smt	Open Pin				
15.00	0.591	.6mm Free Height	.6mm	Smt	Open Pin				
15.00	0.591	.8mm Free Height	.8mm	Smt	Open Pin				
15.00	0.591	1mm Free Height	1mm	Smt	Open Pin				
15.00	0.591	Z-PACK 2mm HM	2mm	Press Fit	Open Pin				
15.00	0.591	STEP-Z Grid Array	Grid	BGA	Controlled Z				
15.00	0.591	Z-PACK TinMan 85ohn	n 1.9mm	Press Fit	Controlled Z				
15.61	0.615	MICTOR	.025"	Smt	Controlled Z				
16.00	0.630	.5mm Free Height	.5mm	Smt	Open Pin				
16.00	0.630	.6mm Free Height	.6mm	Smt	Open Pin				
16.00	0.630	.8mm Free Height	.8mm	Smt	Open Pin				
16.00	0.630	MICTOR SB	.8mm	Smt	Controlled Z				
16.00	0.630	Z-PACK TinMan	1.9mm	Press Fit	Controlled Z				
16.66	0.656	Eurocard (Din)	.100"	Thru-Hole	Open Pin				
17.00	0.669	.8mm Free Height	.8mm	Smt	Open Pin				
				BGA					
17.00	0.669	STEP-Z Grid Array Z-PACK Futurebus +	Grid		Controlled Z				
17.70	0.697		2mm	Press Fit	Open Pin				
17.96	0.707	MICTOR	.025"	Smt	Controlled Z				
18.00	0.709	.6mm Free Height	.6mm	Smt	Open Pin				
18.00	0.709	.8mm Free Height	.8mm	Smt	Open Pin				
18.00	0.709	MICTOR	.025"	Smt	Controlled Z				
18.00	0.709	STEP-Z Grid Array	Grid	BGA	Controlled Z				
18.00	0.709	Micro-Strip	.050"	Thru-Hole	Controlled Z				
18.00	0.709	Z-PACK HM-Zd	2.5mm	Press Fit	Controlled Z				
18.75	0.738	MICTOR	.025"	Smt	Controlled Z				
19.00	0.748	.8mm Free Height	.8mm	Smt	Open Pin				
19.00	0.748	MICTOR SB	.8mm	Smt	Open Pin				
20.00		.6mm Free Height	.6mm	Smt	Open Pin				
20.00		.8mm Free Height	.8mm	Smt	Open Pin				
20.00		MICTOR	.025"	Smt	Controlled Z				
20.00		STEP-Z Grid Array	Grid	BGA	Controlled Z				
21.00	0.787	STEP-Z Grid Array	Grid	BGA	Controlled Z				
21.60	0.827	MICTOR	.025"	Smt	Controlled Z				
	0.866	MICTOR SB	.8mm	Smt	Controlled Z				
	0.900	MICTOR	.025"	Smt	Controlled Z	_			
	0.906	STEP-Z Grid Array	Grid	BGA	Controlled Z				
	0.906	Z-PACK HS3	25mm	Press Fit	Controlled Z				
	0.945	STEP-Z Grid Array	Grid	BGA	Controlled Z	_			
25.00	0.984	MICTOR SB	.8mm	Smt	Controlled Z				
25.00	0.984	STEP-Z Grid Array	Grid	BGA	Controlled Z				
26.00	1.020	STEP-Z Grid Array	Grid	BGA	Controlled Z				
27.00	1.063	MICTOR	.025"	Smt	Controlled Z				
27.00	1.063	STEP-Z Grid Array	Grid	BGA	Controlled Z				
27.80		MICTOR	.025"	Smt	Controlled Z				
28.00		STRADA Mesa	Grid	Press Fit	Controlled Z				
28.00		STEP-Z Grid Array	Grid	BGA	Controlled Z				
29.00		MICTOR	.025"	Smt	Controlled Z				
30.00		MICTOR SB	.023	Smt	Controlled Z				
						+			
30.00		STEP-Z Grid Array	Grid	BGA	Controlled Z	_			
31.00		STEP-Z Grid Array	Grid	BGA	Controlled Z	_			
	1.220	Micro-Strip	.050"	Thru-Hole	Controlled Z	_			
31.88		MICTOR	.025"	Smt	Controlled Z				
35.00		STEP-Z Grid Array	Grid	BGA	Controlled Z				
36.00		STEP-Z Grid Array	Grid	BGA	Controlled Z				
38.94	1.533	Micro-Strip	.050"	Thru-Hole	Controlled Z				
4000	1.575	STEP-Z Grid Array	Grid	BGA	Controlled Z		1		



FINE PITCH SMT STACKING CONNECTORS (PARALLEL BOARD-TO-BOARD)









0.4mm Fine Stack Connectors

- 0.4mm contact pitch
- 1.0mm and 1.5mm stacking height
- 20 to 90 positions

0.5mm Fine Mate Connectors

- 0.5mm contact pitch
- 4.0mm to 6.0mm stacking heights
- 16 to 100 positions
- Right angle options

0.5mm Fine Stack Connectors

- 0.5mm contact pitch
- 1.5mm stacking height
- 20 to 80 positions

0.5mm Free Height (FH) Connectors

- 0.5mm contact pitch
- 5.0mm to 16mm stacking heights
- 120 to 440 positions









O.6mm Free Height (FH) Connectors

- 0.6mm contact pitch
- 4.0mm to 16mm stacking heights
- 50 to 320 positions
- Grounded (GIGA) versions

0.8mm Fine Mate Connectors

- 0.8mm contact pitch
- 4.0mm and 4.5mm stacking heights
- 10 to 60 positions

0.8mm Fine Stack Connectors

- 0.8mm contact pitch
- 3.0mm stacking height
- 14 to 50 positions

O.8mm Free Height (FH) Connectors

- 0.8mm contact pitch
- 5.0mm to 16mm stacking heights
- 40 to 200 positions









1.0mm FH (IEEE 1386) Connectors

- 1.0mm contact pitch
- 8.0mm to 15mm stacking heights
- 64 and 84 positions

AMPMODU 50/50 Grid

- 1.27 [.050] contact pitch
- 6.35 [.250], 8.13 [.320] and 9.91 [.390] stacking heights
- 10 to 100 positions

AMPMODU System 50 Connectors

- 1.27mm [.050"] contact pitch
- 13.08mm [.515"] stacking height
- 10 to 100 positions

Eurocard (Din)

- 0.4mm contact pitch
- 1.0mm and 1.5mm stacking height
- 20 to 90 positions

http://www.tycoelectronics.com



FINE PITCH SMT STACKING CONNECTORS (PARALLEL BOARD-TO-BOARD) CONTINUED









Micro-Strip Connectors

- 1.27mm [.050"] pitch
- 10.92mm to 38.94mm height
- 40-240 positions
- Controlled impedance

MICTOR Connectors

- 0.635mm [.025"] contact pitch
- 6.6mm to 22.86mm [.260" to .900"] stacking heights
- 38-266 positions
- Matched impedance

MICTOR SB Connectors

- 0.8mm pitch
- 5mm to 30mm height
- 40 to 200 positions
- Controlled impedance

STEP-Z Grid Array Connectors

- 1 x 0.65 grid
- 15mm to 40mm height
- 104, 200, 296 positions
- Controlled impedance









STRADA Mesa Connectors

- 3.1 x 2.6 grid
- 8mm to 42mm height
- 130 to 518 positions
- Controlled impedance
- Power options

Z-PACK 2mm HM Connectors

- 2mm pitch
- 15mm height
- 55 positions minimumEnd-to-end stackable

Connectors

- 2mm pitch
- 17.7mm height
- 24 positions minimum

Z-PACK Futurebus +

■ End-to-end stackable

Z-PACK HM-Zd Connectors

- 2.5mm pitch
- 18mm height
- 40 different pairs minimum
- End-to-end stackable
- Controlled impedance







Z-PACK TinMan & Z-PACK TinMan 850hm Connectors

- 1.9mm pitch
- 15mm, 16mm, and 39mm height
- 24 different pair minimum
- Controlled impedanceEnd-to-end stackable

1.25 mm Centerline Fine Pitch Connectors

- 1.25mm fine pitch
- 5mm to 11mm height
- 4 to 30 positionsPin and socket

Z-PACK HS3 Connectors

- 2.5mm pitch
- 23mm height
- 30 positions minimum
- Controlled impedance
- End-to-end stackable

Once you have determined which connector description best suits your needs (using the chart on pages 2 and 3 of this document), use the chart below to find a part number to search the Tyco Electronics website.

	Representative Part Numbers				
Connector Description	Plug	Receptacle			
.4mm Fine Stack	2-1871566-4	2-1747769-4			
.5mm Fine Mate	1565359-1	1565357-1			
.5mm Fine Stack	7-5353164-6	7-5353159-5			
.5mm Free Height	3-6318491-6	3-6318490-6			
.6mm Free Height	1-5353184-0	1-5353190-0			
.8mm Fine Mate	2-5917407-2	2-5917408-2			
.8mm Fine Stack	1-179396-2	1-179397-2			
.8mm Free Height	5177983-4	5177984-4			
1mm Free Height	5120528-1	5120534-1			
AMPMODU 50/50	5-104693-2	5-104652-2			
AMPMODU System 50	5-147377-3	5-104550-4			
Eurocard (Din)	650889-1	5353032-4			
Micro-Strip	5536280-1	5536279-1			
MICTOR	5767007-8	2-5767004-2			
MICTOR SB	1658013-1	1658012-1			
STEP-Z Grid Array	6-1761714-3	5-1761715-5			
STRADA Mesa	2-2057470-8	2057471-1			
Z-PACK 2mm HM	100143-1	106773-1			
Z-PACK Futurebus+	223002-1	223652-1			
Z-PACK HM-Zd	1469002-1	1469362-1			
Z-PACK TinMan	1934312-1	1934544-1			
Z-PACK TinMan 85ohm	1934948-1	1934949-1			
1.25 mm Centerline Fine Pitch	4-176890-6	4-175630-6			
Z-PACK HS3	120732-1	120948-1			


YOU ARE HERE (E-CATALOG)

Link

http://www.tycoelectronics.com/

Do a keyword search for Parallel (Stacking) Configuration or follow the breakdown below.

<u>Breakdown From Main Page</u>



Disclaimer

While Tyco Electronics has made every reasonable effort to ensure the accuracy of the information in this catalog, Tyco Electronics does not guarantee that it is error-free, nor does Tyco Electronics make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current.

Tyco Electronics reserves the right to make any adjustments to the information contained herein at any time without notice. Tyco Electronics expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose.

The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Please consult Tyco Electronics for the latest dimensions and design specifications.

Restriction on the use of Hazardous Substances (RoHS)

At Tyco Electronics, we're ready to support your RoHS requirements. We've assessed more than 1.5 million end items/components for RoHS compliance, and issued new part numbers where any change was required to eliminate the restricted materials. Part numbers in this catalog are identified as:

RoHS Compliant — Part numbers in this catalog are RoHS Compliant, unless marked otherwise. These products comply with European Union Directive 2002/95/EC as amended 1 January 2006 that restricts the use of lead, mercury, cadmium, hexavalent chromium, PBB, and PBDE in certain electrical and electronic products sold into the EU as of 1 July 2006.

NOTE: For purposes of this Catalog, included within the definition of RoHS Compliant are products that are clearly "Out of Scope" of the RoHS Directive such as hand tools and other non-electrical accessories.

NOTE: Information regarding RoHS compliance is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information provided by our suppliers. This information is subject to change. For latest compliance status, refer to our website referenced at right.

Getting the Information You Need

Our comprehensive on-line RoHS Customer Support Center provides a forum to answer your questions and support your RoHS needs. A RoHS FAQ (Frequently Asked Questions) is available with links to more detailed information. You can also submit RoHS questions and receive a response within 24 hours during a normal work week. The Support Center also provides:

- Cross-Reference from Non-compliant to Compliant Products
- Ability to browse RoHS Compliant Products in our on-line catalog
- Downloadable Technical Data Customer Information Presentation
- More detailed information regarding the definitions used above
- So whatever your questions when it comes to RoHS, we've got the answers at www.tycoelectronics.com/leadfree



© 2009 Tyco Electronics Corporation. All Rights Reserved.

TE LOGO, TYCO ELECTRONICS, AMPMODU, MICTOR, STEP-Z, STRADA Mesa, Z-PACK, and Z-PACK TinMan are trademarks. Other products, logos and company names mentioned herein may be trademarks of their respective owners.

Dimensions are in millimeters with inches (if shown) in brackets. Specifications subject to change. For more information, contact your Tyco Electronics sales engineer at the numbers listed below, or visit our Website at: http://www.tycoelectronics.com.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 S. America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 31-73-6246-431



2-1773454-6-1.5K-FP-CIS AH-01/09