


# CLE230W, CLE231W, CLE232W

## High Power Aluminum Gallium Arsenide IREDS



July, 2001



### features

- wide emission angle
- TO-46 hermetically sealed package
- excellent heat dissipation
- high power output

### description

The CLE230W series are AlGaAs infrared emitting diodes mounted in flat window TO-46 hermetic packages. The wide emission angle provides even illumination over a large area. The series are spectrally and mechanically matched to the CLT130W phototransistor series. For additional information, call Clairex.

### absolute maximum ratings ( $T_A = 25^\circ\text{C}$ unless otherwise stated)

storage temperature	-55°C to +150°C
operating temperature	-55°C to +125°C
lead soldering temperature <sup>(1)</sup>	240°C
maximum continuous current <sup>(2)</sup>	100mA
peak forward current (10 $\mu$ s pulse width, 100pps)	10A
maximum power dissipation <sup>(3)</sup>	200mW
reverse voltage	3V

### notes:

1. 0.06" (1.5mm) from the header for 5 seconds maximum. Maximum temperature can be 260°C if wave soldering.
2. Derate linearly 0.80mA/°C from 25°C free air temperature to  $T_A = +125^\circ\text{C}$ .
3. Derate linearly 1.6mW/°C from 25°C free air temperature to  $T_A = +125^\circ\text{C}$ .

### electrical characteristics ( $T_A = 25^\circ\text{C}$ unless otherwise noted)

symbol	parameter		min	typ	max	units	test conditions
$E_e$	Irradiance <sup>(4,5)</sup>	CLE230W	1.5	-	-	mW/cm <sup>2</sup>	$I_F = 100\text{mA}$
		CLE231W	3.5	-	-		
		CLE232W	5.0	-	-		
$V_F$	Forward voltage <sup>(4,5)</sup>		-	-	2.0	V	$I_F = 100\text{mA}$
$I_R$	Reverse current		-	-	10	$\mu\text{A}$	$V_R = 3.0\text{V}$
$\lambda_P$	Peak emission wavelength		-	890	-	nm	$I_F = 100\text{mA}$
BW	Spectral bandwidth at half power points		-	80	-	nm	$I_F = 100\text{mA}$
$\Theta_{HP}$	Emission angle at half power points		-	70	-	deg.	$I_F = 100\text{mA}$
$t_r$	Output rise time		-	500	-	ns	$I_F = 100\text{mA}$
$t_f$	Output fall time		-	250	-	ns	$I_F = 100\text{mA}$

**note:** 4.  $E_e$  is a measure of irradiance (power/unit area) within a .25" (6.35mm) diameter area, centered on the mechanical axis of the device and spaced .466" (11.8mm) from the lens side of the tab. This is geometrically equivalent to a 30° cone.  
5. Measurement taken at trailing edge of 100 $\mu$ s pulse with a duty cycle of 0.1%.

Clairex reserves the right to make changes at any time to improve design and to provide the best possible product.

Revised 12/01/04

Clairex Technologies, Inc.  
Phone: 972-265-4900

1301 East Plano Parkway  
Fax: 972-265-4949

Plano, Texas 75074-8524  
www.clairerx.com