

OPTICAL SENSORS ITR9707

Features

- Fast response time
- High analytic
- Cut-off visible wavelength λp=940nm
- High sensitivity
- Pb free
- This product itself will remain within RoHS compliant version

Descriptions

- The ITR9707 consist of an infrared emitting diode and an NPN silicon phototransistor, encased side-by-side on converging optical axis in a black thermoplastic housing,
- The phototransistor receives radiation from the IR LED only . This is the normal situation.
- But when an object is in between , phototransistor could not receives the radiation.
- For additional component information, please refer to IR908-7C and PT908-7C


Applications

- Mouse Copier
- Switch Scanner
- Floppy disk driver
- Non-contact Switching
- For Direct Board

Device Selection Guide

Device No.	Chip Material	LENS COLOR
IR908-7C	GaAlAs	Water clear
PT908-7C	Silicon	Water clear

Package Dimensions



Notes:

- 1.All dimensions are in millimeters
- 2.Tolerances unless dimensions ±0.2mm
- 3.Lead spacing is measured where the lead emerge from the package
- 4. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification
- 5. These specification sheets include materials protected under copyright of EVERLIGHT corporation . Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent
- 6. When using this product, please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.

Absolute Maximum Ratings (Ta=25℃)

Parameter		Symbol	Ratings	Unit
	Power Dissipation at(or below) 25°C Free Air Temperature	Pd	75	mW
Input	Reverse Voltage	VR	5	V
	Forward Current	IF	50	mA
	Peak Forward Current (*1) Pulse width $\leq 100 \mu$ s, Duty cycle=1%	IFP	1	A
Output	Collector Power Dissipation	Рс	75	mW
	Collector Current	Ic	20	mA
	Collector-Emitter Voltage	Vceo	30	V
	Emitter-Collector Voltage	Veco	5	V
Operating Temperature		Topr	-25~+85	$^{\circ}\!\mathbb{C}$
Storage Temperature		Tstg	-40~+100	$^{\circ}\!\mathbb{C}$
Lead Soldering Temperature (*2) (1/16 inch form body for 5 seconds)		Tsol	260	°C

(*1) tw=100 μ sec., T=10 msec. (*2) t=5 Sec

Electro-Optical Characteristics (Ta=25℃)

Parameter		Symbol	Min.	Тур.	Max.	Unit	Conditions	
	Forward Voltage	V_{F}		1.2	1.5	V	I _F =20mA	
	Reverse Current	I_R			10	μ A	$V_R=5V$	
	Peak Wavelength	λ _P		940		nm	$I_F=20mA$	
	View Angle	2θ1/2		60		Deg	I _F =20mA	
Output	Dark C urrent	I_{CEO}			100	nA	$V_{CE}=20V,Ee=0mW/cm^2$	
	C-E Saturation Voltage	V _{CE} (sat)			0.4	V	$I_C=2mA$ $Ee=1mW/cm^2$	
Transfer Characteristics	Collect Current	$I_{C}(ON)$	0.50			mA	V _{CE} =5V I _F =20mA	
	Rise time	$t_{\rm r}$		15		μ sec	V _{CE} =5V I _C =1mA	
	Fall time	t_{f}		15		$\mu \sec$	$R_L=1K\Omega$	

Typical Electrical/Optical/Characteristics Curves for IR

Fig.1 Forward Current vs.





Fig.2 Spectral Distribution



Wavelength λ (nm)

Fig.3 Peak Emission Wavelength

Ambient Temperature




Fig.4 Forward Current vs.






Fig.8 Forward Current vs. Ambient Temperature(°C)





Fig.6 Relative Radiant Intensity vs. Angular Displacement



Typical Electrical/Optical/Characteristics Curves for PT




Fig.3 Relative Collector Current vs. Ambient Temperature





Fig.5 Spectral Sensitivity

Ambient Temperature Ta (°C)








Fig.4 Collector Current vs. Irradiance



Irradiance Ee (mW/cm²)




Collector-Emitter Voltage Va (V)

Packing Quantity Specification

- 1. 78Pcs/1Tube.42 Tubes/1Box
- 2. 4Boxes/1Carton

Label Form Specification



CPN: Customer's Production Number

P/N : Production Number

QTY: Packing Quantity

CAT: Ranks

HUE: Peak Wavelength

REF: Reference

LOT No: Lot Number

X: Month

Reference: Identify Label Number

Notes

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.

These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.