Optical disc ICs

4-channel BTL driver for CD players BA6297AFP

The BA6297AFP is a 4-channel BTL driver for CD player actuators and motors. The preamplifier has both positive and negative input pins and output pins, making this IC suited to a broad range of applications.

Applications

CD players

Features

- 1) 4-channel BTL driver.
- HSOP 28-pin package allows for miniaturization of applications.
- 3) Internal thermal shutdown.

- Driver gain is adjustable with a single attached resistor.
- 5) Both positive and negative input pins, for adaptability for a wide range of inputs (including negative phase input).

●Absolute maximum ratings (Ta = 25°C)


Parameter	Symbol	Limits	Unit
Power supply voltage	Vcc	18	٧
Power dissipation	Pd	1.7*	W
Operating temperature	Topr	−40~+80	°
Storage temperature	Tstg	−55∼+150	°

When mounted on a 50 mm imes 50 mm imes 1.0 mm paper phenol board

●Recommended operating conditions (Ta = 25°C)

Parameter	Symbol	Symbol Min.		Max.	Unit
Operating power supply voltage	Vcc	6.0	_	9.0	V

Block diagram



●Electrical characteristics (unless otherwise noted, Ta = 25°C, Vcc = 8V, f = 1kHz, RL = 8Ω)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions	Measurement Circuit
Quiescent current dissipation	lα	6.5	11	15.5	mA	No load	
Output offset voltage	Voo	-30	_	30	mV		
Maximum output voltage, high	Vohd	5.2	5.6	_	٧	V _{INDC} =1V	
Maximum output voltage, low	Vold	_	1.3	1.55	٧	V _{INDC} =7V	
Input bias current	lв	_	_	300	nA		
Synchronous input voltage	VICM	1.6	_	6.8	٧	Preamplifier, buffer configured	
Preamplifier VoH	Vohp	6.6	7.1	_	٧	V _{INDC} =GND, R _L =∞	
Preamplifier Vo∟	VOLP	_	0.8	1.3	٧	V _{INDC} =V _{CC} , R _L =∞	Fig.5
Preamplifier Іон	Іонр	2	_	_	mA	Preamplifier output 100 Ωat GND	
Preamplifier IoL	lolp	5	_	_	mA	Preamplifier output 100 Ω at Vcc	
Ripple rejection ratio	RR	-	70	_	dB	V _{IN} =-20dBV, 100Hz	
Slew rate	SR	_	2	_	V/μs	100 kHz square wave, 3VP-P output	
Bias pin voltage	Vref	3.65	3.80	3.95	٧		
Bias voltage variation	△Vref	-30	-	25	mV	1 mA sink / source	
Mute-off voltage	V _{MUTE}	2.0	_	_	٧		

Electrical characteristic curves




Fig. 1 Thermal derating curve




Fig. 2 Power supply voltage vs. output amplitude





Fig. 3 Power supply voltage vs. bias pin voltage



INPUT VOLTAGE: Vin (V)

Fig. 4 Driver I / O characteristics

Measurement circuit




Table 1 Measurement circuit switch

Parameter				Note					
Vin	BIAS	VREF	NF	RL	IPR	IB (+)	RIP	Note	
lα	D	ON	ON	10k	OFF	0	ON	ON	
Voo	→	+	1	+	ON	ţ	+	+	
Vohd	→	OFF	1	+	+	ţ	+	+	V _{INDC} =1V, 7V
Vold	+	ţ	Ţ	Ţ	+	ţ	Ţ	↓	VINDC=1V, 7V
Ів	0	ţ	1	1M	OFF	ţ	OFF	+	Both pin outputs: 1 M Ω
Vісм	+	ON	OFF	SHORT	+	ţ	ON	+	
VOHP	+	OFF	ON	10k	+	ţ	↓	↓	V _{INDC} =GND
Volp	+	↓	1	1	↓	1	1	↓	V _{INDC} =V _{CC}
Іонр	+	↓	Ţ	SHORT	↓	G	Ţ	↓	
lolp	+	ţ	ţ	1	+	V	ţ	↓	
RR	D	ON	ţ	10k	ON	0	ţ	OFF	
Vref	0	+	1	†	+	1	†	ON	
ΔVref	↓	OFF	OFF	+	OFF	ţ	ţ	+	

^{*} Unless otherwise noted, $V_{\text{BIAS}} = V_{\text{INDC}} = 2.5 \text{ V}$

ROHM

Circuit operation

The BA6297AFP comprises a 4-channel driver, internal bias amplifier, mute pin and thermal shutdown.

(1) Driver

The driver uses a buffer to output one of the outputs from its preamplifier with no modification, and uses an inversion amplifier to invert the other output before sending it to the driver buffer. The inversion amplifier's reference is the bias voltage generated internally (pin 7 voltage), and so the preamplifier output must make the zero level equal to the internal bias voltage. See Figs. 7 and 8 for examples.




Fig. 6 Driver block




Fig. 7 Differential input




Fig. 8 Input centered on 2.5 V

(2) Internal bias amplifier

Configured as shown in Fig. 9. The internal bias voltage (V_{ref}) is calculated thus :




Fig. 9 Internal bias block

(3) Mute pin (pin 15)

The output current is muted when this pin receives the low level or a high impedance. Set the pin voltage at high during normal operation.




Fig. 10 The mute pin

(4) Thermal shutdown

The BA6297AFP has an internal thermal shutdown circuit. Output current is muted when the chip temperature exceeds 175°C (typically).

322

Operation notes

- (1) The BA6297AFP has an internal thermal shutdown circuit. Output current is muted when the chip temperature exceeds 175° C (typically).
- (2) If the mute pin (pin 15) voltage is opened or lowered below 0.5V, the output current will be muted. Pin 2 should be pulled up above 2.0V during normal use. During muting, the output pins remain at the internal bias voltage, roughly ($V_{\rm CC}-V_{\rm F}$) / 2.
- (3) Be sure to connect the IC to a $0.1\mu F$ bypass capacitor to the power supply, at the base of the IC.
- (4) The radiating fin is connected to the packages internal GND, but should also be connected to an external ground.

Application example




Fig. 11

External dimensions (Units: mm)

