

SHA2604 THROUGH SHA2607

30 AMP


ULTRA FAST RECOVERY  
CENTERTAP RECTIFIER

200 - 500 VOLTS

X00051  
SSDI14849 FIRESTONE BLVD.  
LA MIRADA, CA 90638  
TEL: (213) 921-9660  
FAX: (213) 921-2396

## CASE STYLE

JEDEC TO-3 with .060 PINS



## FEATURES

- ▶ COMBINED PERFORMANCE OF TWO DO-4 DISCRETES
- ▶ PIV TO 500 VOLTS
- ▶ ULTRA FAST RECOVERY. 35ns TYPICAL
- ▶ HERMETICALLY SEALED
- ▶ SUPERIOR THERMAL RESISTANCE
- ▶ GOLD EUTECTIC DIE ATTACH, NO SOLDER USED
- ▶ ALUMINUM ULTRASONIC WIRE BOND
- ▶ REPLACES UES2604 THROUGH UES2606

## MAXIMUM RATINGS

RATING	SYMBOL	VALUE	UNIT
Peak Repetitive Reverse Voltage Per Leg and DC Blocking Voltage Per Leg SHA2604 SHA2605 SHA2606 SHA2607	VRM(rep) VR	200 300 400 500	Volts
RMS Reverse Voltage Per Leg SHA2604 SHA2605 SHA2606 SHA2607	Vr	140 210 280 350	Volts
Half Wave Rectified Forward Current Averaged Over Full Cycle (Resistive Load, 60Hz, Sine Wave, TC=55 °C)	IO	30	Amps
Peak Repetitive Forward Current (TC=55 °C, 8.3ms Pulse, Allow Junction to Reach Equilibrium Between Pulses)	IFM(rep)	120	Amps
Peak Surge Current (TC=55 °C, 8.3ms Pulse, Superimposed on Rated Current at Rated Voltage)	IFM(surge)	350	Amps
Operating and Storage Temperature	TJ, Tstg	-65 to +200	°C

## THERMAL CHARACTERISTICS

CHARACTERISTIC	SYMBOL	VALUE	UNIT
Thermal Resistance, Junction to Case Both legs tied together	RθJC	1.6	°C/W

Rev. 12/89

G2907

Note: All specifications subject to change without notice.

